



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A320
- ASTM A194 Plain Gr.L7 -
Gr.7 5/8X40 (1.1/2)**

Article number	22325.158.038
Brand	-
UBB	500578887241
UNSPSC	31161619
EAN	8715494429764
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	40 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Technical Specification

B	1.0625
---	--------

Technical Drawing

L (mm)	40
M	15.5

