

## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.7 1.1/8X130 (5.1/8)



Article number	22326.285.130
Brand	-
UBB	500578268491
UNSPSC	31161619
EAN	8715494360319
PKG. of 1	Full Box Only

### Technical Parameters

Diameter (inch)	1.1/8
Length (L) (mm)	130
Length (L) (Inch - ft)	5.1/8

**Info**  
 Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National

### Standards

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

### Technical Specification

B	1.13/16
M	28.2

### Technical Drawing

Threads per inch 8

**FABORY** OF COURSE.  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS

