



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A320
- ASTM A194 Plain Gr.L7 -
Gr.7 1.1/8X145 (5.3/4)**

Article number	22326.285.146
Brand	-
UBB	500578268723
UNSPSC	31161619
EAN	8715494360340
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/8 Inch
Length	145 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	--

Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Technical Specification

B	1.8125
L (mm)	145

Technical Drawing

