



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.4 2 Inch X750 (29.1/2)

Article number	22330.508.749
Brand	-
UBB	500578967357
UNSPSC	31161619
EAN	8715494426169
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	2 Inch
Length	750 mm
Class	Gr.L7 - Gr.4
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

### Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

**FABORY** It is advised to  
use Grade 7 nuts  
instead.

### Technical Specification

B	3.125
L (mm)	750
M	50

### Technical Drawing

