



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.4 2.3/4X730 (28.3/4)

Article number	22330.698.730
Brand	-
UBB	500578973033
UNSPSC	31161619
EAN	8715494398596
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.3/4 Inch
Length	730 mm
Class	Gr.L7 - Gr.4
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

FABORY It is advised to
use Grade 7 nuts
instead.

Technical Specification

B	4.25
L (mm)	730
M	68.7

Technical Drawing

