



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Stainless steel ASTM
A193 - ASTM A194 Gr.B8
Cl.2 - Gr.8 5/8X140 (5.1/2)**

Article number	22529.158.139
Brand	-
UBB	500578419623
UNSPSC	31161619
EAN	8715494353694
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	140 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	11
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

Technical Specification

B	1.0625
L (mm)	140

Technical Drawing

