



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8 Cl.2 - Gr.8 5/8X175 (6.7/8)

| | |
|----------------|---------------|
| Article number | 22529.158.175 |
| Brand | - |
| UBB | 500578420365 |
| UNSPSC | 31161619 |
| EAN | 8715494353762 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|--|
| Diameter | 5/8 Inch |
| Length | 175 mm |
| Class | Gr.B8 Cl.2 - Gr.8 |
| Material | Stainless steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Thread | Unified National Coarse |
| Threads per inch | 11 |
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |

Standards

| | |
|------|---------------|
| ASME | B16.5/B18.2.2 |
| BS | ≈4882 |
| ASTM | A193/A194 |

Technical Specification

| | |
|--------|--------|
| B | 1.0625 |
| L (mm) | 175 |

Technical Drawing

