



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Stainless steel ASTM
A193 - ASTM A194 Gr.B8
Cl.2 - Gr.8 1.5/8X545 (21.1/2)**

Article number	22530.412.546
Brand	-
UBB	500578564402
UNSPSC	31161619
EAN	8715494361545
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.5/8 Inch
Length	545 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Technical Specification

B	2.5625
L (mm)	545
M	40.5

Technical Drawing

FABORY

