



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Stainless steel ASTM
A193 - ASTM A194 Gr.B8
Cl.2 - Gr.8 2.1/2X435 (17.1/8)**

Article number	22530.635.435
Brand	-
UBB	500578584129
UNSPSC	31161619
EAN	8715494352758
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.1/2 Inch
Length	435 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Technical Specification

B	3.3125
L (mm)	435
M	62.3

Technical Drawing

FABORY

