



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8 - Gr.8 7/8X495 (19.1/2)

Article number	22534.222.495
Brand	-
UBB	500578996976
UNSPSC	31161619
EAN	8715494412599
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	495 mm
Class	Gr.B8 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	9
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	1.4375
L (mm)	495

Technical Drawing

