



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 7/8X205 (8.1/8)

Article number	22538.222.205
Brand	-
UBB	500578054479
UNSPSC	31161619
EAN	8715494333191
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	205 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	9
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

Technical Specification

B	1.4375
L (mm)	205

Technical Drawing

