



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Stainless steel ASTM
A193 - ASTM A194 Gr.B8M
Cl.2 - Gr.8M 1.1/4X205 (8.1/8)**

Article number	22539.317.205
Brand	-
UBB	500578144239
UNSPSC	31161619
EAN	8715494326735
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/4 Inch
Length	205 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	2
L (mm)	205
M	31

Technical Drawing

FABORY

