



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 1.1/4X355 (14)

Article number	22539.317.355
Brand	-
UBB	500578147208
UNSPSC	31161619
EAN	8715494321235
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	1.1/4 Inch
Length	355 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

### Technical Specification

B	2
L (mm)	355
M	31

### Technical Drawing

FABORY

