



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Stainless steel ASTM  
A193 - ASTM A194 Gr.B8M  
Cl.2 - Gr.8M 1.7/8X465  
(18.1/4)**

Article number	22539.476.463
Brand	-
UBB	500578181926
UNSPSC	31161619
EAN	8715494318884
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	1.7/8 Inch
Length	465 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

**Technical Specification**

B	2.9375
---	--------

**Technical Drawing**

L (mm)	465
M	46.8

