



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Stainless steel ASTM
A193 - ASTM A194 Gr.B8M
Cl.2 - Gr.8M 2.1/2X585 (23)**

Article number	22539.635.584
Brand	-
UBB	500578192402
UNSPSC	31161619
EAN	8715494349741
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.1/2 Inch
Length	585 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

Technical Specification

B	3.3125
L (mm)	585
M	62.3

Technical Drawing

FABORY

