



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193 -
ASTM A194 Plain Gr.B16 -
Gr.4 1/2X110 (4.1/4)**

| | |
|----------------|---------------|
| Article number | 22554.127.107 |
| Brand | - |
| UBB | 500579038950 |
| UNSPSC | 31161619 |
| EAN | 8715494413466 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|-------------------------|
| Diameter | 1/2 Inch |
| Length | 110 mm |
| Class | Gr.B16 - Gr.4 |
| Material | Steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Unified National Coarse |
| Threads per inch | 13 |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased |
|------|---|

Standards

| | |
|------|---------------|
| ASME | B16.5/B18.2.2 |
| BS | ≈4882 |
| ASTM | A193/A194 |

out gradually.
It is advised to
use Grade 7 nuts
instead.

Technical Specification

| | |
|--------|-------|
| B | 0.875 |
| L (mm) | 110 |
| M | 12.3 |

Technical Drawing

