



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 1.3/8X200 (8)

Article number	22555.349.203
Brand	-
UBB	500578221524
UNSPSC	31161619
EAN	8715494356480
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	1.3/8 Inch
Length	200 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

### Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

**FABORY** It is advised to  
use Grade 7 nuts  
instead.

### Technical Specification

B	2.1875
L (mm)	200
M	34.1

### Technical Drawing

