



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 2 Inch X565 (22.1/4)

Article number	22555.508.565
Brand	-
UBB	500578258252
UNSPSC	31161619
EAN	8715494356831
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2 Inch
Length	565 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

FABORY It is advised to
use Grade 7 nuts
instead.

Technical Specification

B	3.125
L (mm)	565
M	50

Technical Drawing

