



**Double end stud with
reduced shank with 2
hexagon nuts DIN 2510 L/
NF Steel 21CrMoV5-7+QT
(1.7709)/25CrMo4+QT
(1.7218) Plain M12X85**

Article number	23530.120.085
Brand	-
UBB	500644894668
UNSPSC	31161619
EAN	8717077038868
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	85 mm
Marking	GA/KG
Material	Steel
Material technical	21CrMoV5-7+QT (1.7709)/25CrMo4+QT (1.7218)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	External thread with large clearance according to DIN 2510-2.

Standards

DIN	2510-L/NF
-----	-----------

Technical Specification

b	20
d-D	M12
d2	8.5
L (mm)	85
m	12
P	1.75

Technical Drawing



