



Slotted cheese head screw DIN 84 Steel Zinc plated 8.8 M2X12

Article number	24402.020.012
Brand	-
UBB	951353056967
UNSPSC	31161504
EAN	8715492626981
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	12 mm
Class	8.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-127
ASME	≈B18.6.7M
NEN	≈1602
DIN	84
ISO	≈1207

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	12
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing