



## Slotted countersunk head screw DIN 963 Steel Zinc plated 8.8 M3X6

|                |               |
|----------------|---------------|
| Article number | 24412.030.006 |
| Brand          | -             |
| UBB            | 951353063062  |
| UNSPSC         | 31161504      |
| EAN            | 8715492627582 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M3               |
| Length            | 6 mm             |
| Class             | 8.8              |
| Driving features  | Slotted          |
| Head shape        | Countersunk head |
| Material          | Steel            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

### Standards

|      |           |
|------|-----------|
| ISO  | ≈2009     |
| NF   | ≈E25-123  |
| ASME | ≈B18.6.7M |
| DIN  | 963       |
| BS   | ≈4183     |
| NEN  | ≈2370     |

### Technical Specification

|                         |      |
|-------------------------|------|
| d-D                     | M3   |
| Thread length (min.)    | 19   |
| dk (max.)               | 5.6  |
| Full thread if $L \leq$ | 22   |
| k (max.)                | 1.65 |
| L (mm)                  | 6    |
| n                       | 0.8  |
| P                       | 0.5  |
| t (min.)                | 0.6  |

### Technical Drawing

