



Slotted cheese head screw DIN 84 Steel Zinc plated yellow passivated 4.8 M2X16

Article number	24510.020.016
Brand	-
UBB	951353018934
UNSPSC	31161504
EAN	8715492628107
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	≈E25-127
DIN	84
ISO	≈1207
NEN	≈1602
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	16
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing