



Slotted cheese head screw DIN 84 Steel Zinc plated yellow passivated 4.8 M2,5X8

Article number	24510.025.008
Brand	-
UBB	950353676899
UNSPSC	31161504
EAN	8715492628152
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈1602
ISO	≈1207
NF	≈E25-127
ASME	≈B18.6.7M
DIN	84

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	4.5
Full thread if L ≤	30
k (max.)	1.6
L (mm)	8
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing