



Slotted cheese head screw DIN 84 Steel Zinc plated yellow passivated 4.8 M2,5X20

Article number	24510.025.020
Brand	-
UBB	950353793793
UNSPSC	31161504
EAN	8715492628190
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	≈E25-127
BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207
DIN	84

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	4.5
Full thread if L ≤	30
k (max.)	1.6
L (mm)	20
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing