



**Slotted cheese head screw
DIN 84 Steel Zinc plated 4.8
M2X3**

Article number	24520.020.003
Brand	-
UBB	950353815240
UNSPSC	31161504
EAN	8715492629647
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M2
Length	3 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
ISO	≈1207
BS	≈4183
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	3
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing