

## Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M2X8



Article number	24520.020.008
Brand	-
UBB	950353111335
UNSPSC	31161504
EAN	8715492629685
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	8
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	84
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-127
ISO	≈1207

### Technical Specification

Thread length (min.)	25
$d_k$ (max.)	3.8
Full thread if $L \leq$	30
$k$ (max.)	1.3
$n$	0.5
$P$	0.40
$t$ (min.)	0.5

### Technical Drawing

