

Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M2X12



Article number	24520.020.012
Brand	-
UBB	950353111582
UNSPSC	31161504
EAN	8715492629708
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	12
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈1207
NF	≈E25-127
DIN	84
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	25
d_k (max.)	3.8
Full thread if $L \leq$	30
k (max.)	1.3
n	0.5
P	0.40
t (min.)	0.5

Technical Drawing

