



**Slotted cheese head screw
DIN 84 Steel Zinc plated 4.8
M2X16**

Article number	24520.020.016
Brand	-
UBB	950353111665
UNSPSC	31161504
EAN	8715492629722
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-127
DIN	84
BS	≈4183
ASME	≈B18.6.7M
ISO	≈1207
NEN	≈1602

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	16
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing