FABORY

Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M2X18

Article number	24520.020.018
Brand	-
UBB	500645191635
UNSPSC	31161504
EAN	8717077069794
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	18 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈1207
DIN	84
NF	≈E25-127
ASME	≈B18.6.7M
NEN	≈1602

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	18
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing