



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M2,5X4

Article number	24520.025.004
Brand	-
UBB	950353112085
UNSPSC	31161504
EAN	8715492629845
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	4 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈1602
ASME	≈B18.6.7M
DIN	84
NF	≈E25-127
ISO	≈1207
BS	≈4183

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	4.5
Full thread if L ≤	30
k (max.)	1.6
L (mm)	4
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing