



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M3X18

Article number	24520.030.018
Brand	-
UBB	500645192054
UNSPSC	31161504
EAN	8717077069831
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	18 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-127
ISO	≈1207
NEN	≈1602
DIN	84
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	5.5
Full thread if L ≤	30
k (max.)	2
L (mm)	18
n	0.8
P	0.5
t (min.)	0.85

Technical Drawing