



## Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M3,5X5

|                |               |
|----------------|---------------|
| Article number | 24520.035.005 |
| Brand          | -             |
| UBB            | 500645192476  |
| UNSPSC         | 31161504      |
| EAN            | 8717077069879 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M3.5             |
| Length            | 5 mm             |
| Class             | 4.8              |
| Driving features  | Slotted          |
| Head shape        | Cylindrical head |
| Material          | Steel            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

### Standards

|      |           |
|------|-----------|
| NF   | ≈E25-127  |
| DIN  | 84        |
| ISO  | ≈1207     |
| ASME | ≈B18.6.7M |
| BS   | ≈4183     |
| NEN  | ≈1602     |

### Technical Specification

|                      |      |
|----------------------|------|
| d-D                  | M3.5 |
| Thread length (min.) | 38   |
| dk (max.)            | 6    |
| Full thread if L ≤   | 40   |
| k (max.)             | 2.4  |
| L (mm)               | 5    |
| n                    | 1    |
| P                    | 0.6  |
| t (min.)             | 1    |

### Technical Drawing