



**Slotted cheese head screw
DIN 84 Steel Zinc plated 4.8
M5X50**

Article number	24520.050.050
Brand	-
UBB	950353118447
UNSPSC	31161504
EAN	8715492630780
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈1602
DIN	84
ISO	≈1207
BS	≈4183
NF	≈E25-127

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	50
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing