

Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M5X55



Article No.	24520.050.055
Brand	-
UBB	951353041290
UNSPSC	31161504
EAN	8715492630797
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	55
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	4183
ISO	1207
ASME	B18.6.7M
DIN	84
NF	E25-127

Technical Specification

d_k	8.5
Full thread if $L \leq$	40
k	3.3
n	1.2
P	0.80

Technical Drawing

