



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M5X60

Article number	24520.050.060
Brand	-
UBB	950353118512
UNSPSC	31161504
EAN	8715492630803
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
DIN	84
NF	≈E25-127
NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	60
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing