



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M5X100

Article number	24520.050.100
Brand	-
UBB	950353118850
UNSPSC	31161504
EAN	8715492630841
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
DIN	84
ISO	≈1207
NEN	≈1602
NF	≈E25-127

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	8.5
Full thread if L ≤	40
k (max.)	3.3
L (mm)	100
n	1.2
P	0.8
t (min.)	1.3

Technical Drawing