

## Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X10



Article No.	24520.060.010
Brand	-
UBB	950353119015
UNSPSC	31161504
EAN	8715492630865
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	10
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

ASME	B18.6.7M
ISO	1207
NF	E25-127
DIN	84
BS	4183

### Technical Specification

$d_k$	10
Full thread if $L \leq$	40
k	3.9
n	1.6
P	1

### Technical Drawing

