



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X60

Article number	24520.060.060
Brand	-
UBB	950353335090
UNSPSC	31161504
EAN	8715492630995
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-127
DIN	84
NEN	≈1602

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3.9
L (mm)	60
n	1.6
P	1
t (min.)	1.6

Technical Drawing