



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X25

Article number	24520.080.025
Brand	-
UBB	950353120997
UNSPSC	31161504
EAN	8715492631183
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
ASME	≈B18.6.7M
BS	≈4183
ISO	≈1207
NEN	≈1602
NF	≈E25-127

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	25
n	2
P	1.25
t (min.)	2

Technical Drawing