



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X30

Article number	24520.080.030
Brand	-
UBB	950353121078
UNSPSC	31161504
EAN	8715492631190
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	30
n	2
P	1.25
t (min.)	2

Technical Drawing