



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X70

Article number	24520.080.070
Brand	-
UBB	950353121649
UNSPSC	31161504
EAN	8715492631275
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
BS	≈4183
DIN	84
NEN	≈1602

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	70
n	2
P	1.25
t (min.)	2

Technical Drawing