



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X100

Article number	24520.080.100
Brand	-
UBB	950353121805
UNSPSC	31161504
EAN	8715492631305
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	84
BS	≈4183
ISO	≈1207
NEN	≈1602
ASME	≈B18.6.7M
NF	≈E25-127

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	13
Full thread if L ≤	40
k (max.)	5
L (mm)	100
n	2
P	1.25
t (min.)	2

Technical Drawing