



## Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M10X60

|                |               |
|----------------|---------------|
| Article number | 24520.100.060 |
| Brand          | -             |
| UBB            | 950353122639  |
| UNSPSC         | 31161504      |
| EAN            | 8715492631442 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M10              |
| Length            | 60 mm            |
| Class             | 4.8              |
| Driving features  | Slotted          |
| Head shape        | Cylindrical head |
| Material          | Steel            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

### Standards

|      |           |
|------|-----------|
| BS   | ≈4183     |
| DIN  | 84        |
| ASME | ≈B18.6.7M |
| ISO  | ≈1207     |
| NF   | ≈E25-127  |
| NEN  | ≈1602     |

### Technical Specification

|                      |     |
|----------------------|-----|
| d-D                  | M10 |
| Thread length (min.) | 38  |
| dk (max.)            | 16  |
| Full thread if L ≤   | 40  |
| k (max.)             | 6   |
| L (mm)               | 60  |
| n                    | 2.5 |
| P                    | 1.5 |
| t (min.)             | 2.5 |

### Technical Drawing