



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M12X80

Article number	24520.120.080
Brand	-
UBB	950353123884
UNSPSC	31161504
EAN	8715492631596
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-127
ASME	≈B18.6.7M
BS	≈4183
ISO	≈1207
DIN	84
NEN	≈1602

Technical Specification

d-D	M12
Thread length (min.)	38
dk (max.)	18
Full thread if L ≤	40
k (max.)	7
L (mm)	80
n	3
P	1.75
t (min.)	3

Technical Drawing