

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2X4



Article number	24540.020.004
Brand	-
UBB	950353128750
UNSPSC	31161504
EAN	8715492632432
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	4
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
ISO	≈2009
DIN	963
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	16
d_k (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
n	0.5
P	0.40
t (min.)	0.4

Technical Drawing

