



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M2X5

Article number	24540.020.005
Brand	-
UBB	950353128834
UNSPSC	31161504
EAN	8715492632449
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	5 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370
DIN	963

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	5
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

