

Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M2X8



Article number	24540.020.008
Brand	-
UBB	950353129097
UNSPSC	31161504
EAN	8715492632463
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	8
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.6.7M
NF	E25-123
ISO	2009
BS	4183
DIN	963 A

Technical Specification

Thread length (min.)	16
d_k (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
n	0.5
P	0.40
t (min.)	0.4

Technical Drawing

