



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2X10

Article number	24540.020.010
Brand	-
UBB	950353129170
UNSPSC	31161504
EAN	8715492632470
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
NEN	≈2370
DIN	963
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	10
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

