



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M2X20

Article number	24540.020.020
Brand	-
UBB	950353129410
UNSPSC	31161504
EAN	8715492632524
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
NEN	≈2370
ISO	≈2009
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	20
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

