



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2X25

Article number	24540.020.025
Brand	-
UBB	950353129584
UNSPSC	31161504
EAN	8715492632531
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M
DIN	963
NEN	≈2370
BS	≈4183

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	25
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

